

## Product data sheet

### Characteristics

# 31HA-WE

## SWITCH 1 GANG HORIZONTAL STANDARD

### PTN 10A 25



#### Main

Range of product	Standard Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate

#### Complementary

Switch function	2-way 1-way
Number of rocker	1
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	7.3 cm
Package 1 Length	11.5 cm
Package 1 Weight	55.65 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12 cm
Package 2 Width	13.8 cm
Package 2 Length	15.3 cm
Package 2 Weight	0.644 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	38 cm
Package 3 Width	35.5 cm
Package 3 Length	46 cm
Package 3 Weight	11.7 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>