

## Product data sheet

### Characteristics

# 31VCS-WE

## Cooker Socket Outlet, 250VAC, 32A, 3 Pin



### Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
Material	Plastic
[In] rated current	32 A
[Ue] rated operational voltage	250 V AC
Depth	11 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	12.5 cm
Package 1 Length	18.6 cm
Package 1 Weight	106 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8.8 cm
Package 2 Width	16 cm
Package 2 Length	18.8 cm
Package 2 Weight	614 g
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	6.4 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>