

Product data sheet

Characteristics

31VK2/2-WE

Standard Series, Switch, 1 Gang, 250VAC, 20A, 2 Way, Locks in On and Off Position, Key Operated



Main

| | |
|---------------------|-------------------------------------|
| Range of product | Standard Series |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |

Complementary

| | |
|--------------------------------|---------------------------------|
| Switch function | 2-way |
| Device mounting | Flush |
| Fixing mode | By screws |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC |
| Rated current | 20 A 16 AX, fluorescent lamp |
| Marking | ON-OFF |
| Actuator | Key |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4 cm |
| Package 1 Width | 7.3 cm |
| Package 1 Length | 11.7 cm |
| Package 1 Weight | 106.8 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 11.7 cm |
| Package 2 Width | 10.2 cm |
| Package 2 Length | 13.8 cm |
| Package 2 Weight | 0.55 kg |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 100 |
| Package 3 Height | 25.4 cm |
| Package 3 Width | 34.8 cm |
| Package 3 Length | 44.5 cm |
| Package 3 Weight | 11 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |