

## Product data sheet

### Characteristics

# 31VK2/2-WE

Switch, Standard Series, 1 Gang, 250VAC, 20A, 2 Way, Locks in On and Off Position, Key Operated



#### Main

Range of product	Standard Series
Product brand	Clipsal
Assembly Type	Basic element with full cover plate

#### Complementary

Installation Type	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A 16 AX, fluorescent lamp
Marking	ON-OFF
Mounting Type	By screws
Actuator	Key
Switch function	2-way

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.3 cm
Package 1 Length	11.7 cm
Package 1 Weight	106.8 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations