

## Product data sheet

### Characteristics

# 32/2VA-WE

## SWITCH 2 GANG 10A 250V 115MM



### Main

Range of product	Standard Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid






### Complementary

Switch function	2-way 1-way
Number of rocker	2
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	98.8 g
Package 1 Height	26 mm
Package 1 width	115 mm
Package 1 Length	115 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>