

Product data sheet

Characteristics

33/2VA-WE

SWITCH 3G 10A 250V 115MM SQ



Main

| | |
|---------------------|-------------------------------------|
| Range of product | Standard Series |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |

Complementary

| | |
|--------------------------------|-----------------|
| Switch function | 2-way 1-way |
| Actuator | Rocker |
| Number of rocker | 3 |
| Device mounting | Flush |
| Fixing mode | By screws |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC |
| Rated current | 10 A |
| Marking | Without marking |

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 0.140 kg |
|------------------|----------|

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |