

## Product data sheet

### Characteristics

# 357WF40

## SCRW S/D 10GX40 WAFER HD PK100



### Main

|               |         |
|---------------|---------|
| Product brand | Clipsal |
|---------------|---------|

### Complementary

|                     |                             |
|---------------------|-----------------------------|
| Screw gauge         | 10g                         |
| Length              | 40 mm                       |
| Shape of screw head | Pozidriv No 2<br>Wafer head |
| Screwdriver shape   | Phillips                    |
| Size of screw head  | 9 mm                        |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Weight             | 484 g   |
| Package 1 Height             | 4.2 cm  |
| Package 1 width              | 7.2 cm  |
| Package 1 Length             | 14.5 cm |
| Unit Type of Package 2       | BB1     |
| Number of Units in Package 2 | 5       |
| Package 2 Weight             | 2.42 kg |
| Package 2 Height             | 9.2 cm  |
| Package 2 width              | 15 cm   |
| Package 2 Length             | 23 cm   |
| Package 3 Height             | 23.7 cm |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |