

Product data sheet

Characteristics

363-WE

SWITCH SURFACE 2WAY 4TERM



Main

Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	2-way
Control type	Toggle
Device mounting	Surface
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	42.0 g
Package 1 Height	3.3 cm
Package 1 width	5.1 cm
Package 1 Length	5.2 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Weight	4.9 kg
Package 2 Height	23.7 cm
Package 2 width	20.3 cm
Package 2 Length	30 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	236.0 g
Package 3 Height	8 cm
Package 3 width	6 cm
Package 3 Length	12.2 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile