

Product data sheet

Characteristics

39/2VA-WE

SWITCH 9G 10A 250V 115MM SQ



Main

| | |
|---------------------|-------------------------------------|
| Range of product | Standard Series |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |


Complementary

| | |
|--------------------------------|-----------------|
| Switch function | 1-way 2-way |
| Actuator | Rocker |
| Number of rocker | 9 |
| Device mounting | Flush |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC |
| Rated current | 10 A |
| Marking | Without marking |

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 0.078 kg |
|------------------|----------|

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.