

Product data sheet

Characteristics

39M-WE

Switch, Clipsal - Mechanisms, 1 Pole, 250VAC, 10A, 3 Position



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Assembly Type	Basic element

Complementary



Control type	Rotary knob
Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	HIGH-OFF-LOW
Marking location	Marking on surface
Mounting Type	Clip-in
Surface finish	Glossy
Switch function	1-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	2.2 cm
Package 1 Length	3.2 cm
Package 1 Weight	15.2 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
