

## Product data sheet

### Characteristics

# 39MAOM-WE

## SWITCH MECH AUTO/OFF/MAN



### Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

### Complementary

Switch function	1-pole
Control type	Rotary knob
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	Clip-in
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	AUTO-O-MAN
Marking location	Marking on surface

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	12 g
Package 1 Height	2 cm
Package 1 width	2 cm
Package 1 Length	3 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	134 g
Package 2 Height	4.2 cm
Package 2 width	5.6 cm
Package 2 Length	11.6 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	700 g
Package 3 Height	10.2 cm
Package 3 width	12 cm
Package 3 Length	17 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>