

Product data sheet

Characteristics

39MSON-WE

Clipsal - Mechanisms, Switch, 250VAC, 10A, 3 Position



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Device presentation	Basic element




Complementary

Switch function	1-pole
Control type	Rotary knob
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	Clip-in
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	SENSOR-OFF-ON
Marking location	Marking on surface

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	2.2 cm
Package 1 Length	3.2 cm
Package 1 Weight	15.2 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations