

Product data sheet

Characteristics

4015L-PW

Socket Outlet Saturn - Single switched - Assembled - Horizontal - For lighting - 250 V - 10 A - Pure White



Main

Colour	Pure white
Product brand	Clipsal
Range of product	Saturn Series

Complementary

Colour code	PW
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Indicator light
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	36 mm
Embedding depth	22 mm
Length	116 mm
Width	116 mm
Height	75 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Package 1 Weight	140.000 g
Package 1 Height	40.000 mm
Package 1 width	77.000 mm
Package 1 Length	120.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile