

Product data sheet

Characteristics

4015L-PW

Clipsal Saturn 4000 Single Switch Power Point with Round Earth, 250V, 10A



Main

Range of product	Saturn Series
Product brand	Clipsal
Colour	Pure white

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Embedding depth	22 mm
Depth	36 mm
Height	75 mm
Length	116 mm
Width	116 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.7 cm
Package 1 Length	12 cm
Package 1 Weight	140.2 g

Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	130 cm
Package 2 Width	188 cm
Package 2 Length	192 cm
Package 2 Weight	1.57 kg
Package 3 Height	89 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile