

Product data sheet

Characteristics

402-WE

SOCKET 2PIN FLAT



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	110 V AC
Depth	28 mm
Diameter	45 mm
Fixing center	28 mm
Number of poles	1

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	32.0 g
Package 1 Height	2.8 cm
Package 1 width	4.1 cm
Package 1 Length	4.1 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	125
Package 2 Weight	5.25 kg
Package 2 Height	25 cm
Package 2 width	21.4 cm
Package 2 Length	33.8 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5

Package 3 Weight	0.192 kg
Package 3 Height	7 cm
Package 3 width	8.2 cm
Package 3 Length	11 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile