

Product data sheet

Characteristics

4025-PW

Socket Outlet Saturn - Twin switched - Assembled - Horizontal - 250 V - 10 A - Pure White



Main

Range of product	Saturn Series
Product brand	Clipsal
Colour	Pure white

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Embedding depth	15 mm
Depth	29 mm
Height	75 mm
Length	116 mm
Width	116 mm
Fixing center	84 mm

Environment

Product certifications	RCM
Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	112.0 g
Package 1 Height	4.2 cm
Package 1 width	13 cm
Package 1 Length	8.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile