

Product data sheet

Characteristics

4025X-PW

Double Switch Power Point, Saturn Series,
250V, 10A, Non-removable, Extra Switch

Main

Range of product	Saturn Series
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Embedding depth	15 mm
Depth	29 mm
Height	75 mm
Length	116 mm
Width	116 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	9.1 cm
Package 1 Length	12.4 cm
Package 1 Weight	118 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No