

Product data sheet

Characteristics

405/32-WE

SOCKET 2PIN FLUSH 32VOLT



Main

| | |
|------------------|------------------|
| Colour | White electric |
| Product brand | Clipsal |
| Quantity per set | Set of 1 |
| Cover type | Complete housing |

Complementary

| | |
|--------------------------------|-------------------------|
| Colour code | WE |
| Marking | Extra low voltage |
| Local signalling | Without light indicator |
| Device mounting | Flush |
| Fixing mode | By screws |
| [In] rated current | 15 A |
| [Ue] rated operational voltage | 32 V DC |
| Depth | 23 mm |
| Length | 94 mm |
| Width | 42 mm |
| Fixing center | 84 mm |

Environment

| | |
|-----------|--|
| Standards | AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1 |
|-----------|--|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.048 kg |
| Package 1 Height | 23 mm |
| Package 1 width | 42 mm |
| Package 1 Length | 94 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |