

Product data sheet

Characteristics

405/32-WE

Standard Series, Single Socket Outlet, 32V, 10A, 2 PIN, Flush Mount



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Extra low voltage
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	15 A
[Ue] rated operational voltage	32 V DC
Depth	23 mm
Length	94 mm
Width	42 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	4.2 cm
Package 1 Length	9.4 cm
Package 1 Weight	0.048 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes