

Product data sheet

Characteristics

405/32LB-WE

SOCKET 2 PIN FLUSH 32VOLT LB



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
[In] rated current	15 A
[Ue] rated operational voltage	32 V DC
Depth	23 mm
Length	94 mm
Width	42 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	29.0 g
Package 1 Height	3.5 cm
Package 1 width	2.5 cm
Package 1 Length	6.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.35 kg
Package 2 Height	6.5 cm
Package 2 width	9.4 cm
Package 2 Length	13 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	7.0 kg

Package 3 Height	23.3 cm
Package 3 width	29 cm
Package 3 Length	29.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile