

Product data sheet

Characteristics

4061D32-PW

Switch Saturn - Assembled - Cooker - Double-pole - 415 V - 32 A - Pure White



Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	2-pole
Number of poles	2
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	415 V AC
Rated current	32 A
Marking	Without marking
Height	116 mm
Width	75 mm
Depth	37 mm
Embedding depth	23 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	234.0 g
Package 1 Height	9 cm
Package 1 width	6.2 cm
Package 1 Length	12 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	1.28 kg
Package 2 Height	12.2 cm
Package 2 width	10 cm
Package 2 Length	36.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	13.35 kg
Package 3 Height	36 cm

Package 3 width	34.5 cm
Package 3 Length	40.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile