

Product data sheet

Characteristics

4061D32-PW

Flush Switch, Saturn Series, 1 Gang, 2 Pole,
415VAC, Push Button

Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Assembly Type	Basic element

Complementary

Number of poles	2
Installation Type	Flush
Local signalling	without
[Ue] rated operational voltage	415 V AC
Rated current	32 A
Marking	Without marking
Mounting Type	By screws
Height	116 mm
Width	75 mm
Depth	37 mm
Embedding depth	23 mm
Switch function	2-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9 cm
Package 1 Width	6.2 cm
Package 1 Length	12 cm
Package 1 Weight	234 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	12.2 cm
Package 2 Width	10 cm
Package 2 Length	36.4 cm
Package 2 Weight	1.28 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No