

## Product data sheet

### Characteristics

# 4061E2RUDM-TR

## Clipsal Saturn 4000, Rotary Controlled Integrally Switched Universal Dimmer, 350VA



### Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Device presentation	Basic element with full cover plate
Dimmer type	Universal

### Complementary

Power consumption in VA	350 VA
Network frequency	50 Hz
Mounting support	Wall
Width	75 mm
Height	116 mm
Depth	56 mm
Embedding depth	34 mm

### Environment




Standards	AS/NZS 3100 IEC 60669-2-1 AS/NZS CISPR 15 IEC 61000-3-2
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.02 cm
Package 1 Width	0.08 cm
Package 1 Length	0.11 cm
Package 1 Weight	0.06 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>