

Product data sheet

Characteristics

4061E2RUDM-TR

Dimmer 60 Series Module - Universal - Rotary - Integrated Switch - 250 V - Translucent



Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Device presentation	Basic element with full cover plate
Dimmer type	Universal
Colour	Transparent

Complementary

Power consumption in VA	350 VA
Network frequency	50 Hz
Mounting support	Wall
Width	75 mm
Height	116 mm
Depth	56 mm
Embedding depth	34 mm

Environment

Standards	AS/NZS 3100 IEC 60669-2-1 AS/NZS CISPR 15 IEC 61000-3-2
-----------	--

Packing Units

Package 1 Weight	35.460 g
Package 1 Height	0.020 mm
Package 1 width	0.080 mm
Package 1 Length	0.110 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure

 [Product Environmental Profile](#)

Circularity Profile

 [End Of Life Information](#)
