

Product data sheet

Characteristics

4061E4RUD-PW

DIMMER UNIVERSAL ISRC 800W SATURN 4000 SERIES INCLUDING SATURN HORIZON



Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Device presentation	Basic element with full cover plate
Dimmer type	Universal
Colour	Pure white

Complementary

Power consumption in VA	10...800 VA
Network frequency	50 Hz
Mounting support	Wall
Fixing mode	By screws

Environment

Standards	AS/NZS 3100 IEC 60669-2-1 AS/NZS CISPR 15 IEC 61000-3-2
-----------	--

Packing Units

Package 1 Weight	215.000 g
Package 1 Height	70.000 mm
Package 1 width	91.000 mm
Package 1 Length	117.000 mm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.