

Product data sheet

Characteristics

4062AL-PW

Clipsal Saturn 4000, Push Button Switch LED Architrave, 2 Gang, 250V, 16AX/20A



Main

| | |
|---------------------------|-------------------------------------|
| Range of product | Saturn Series 4000 |
| Product or component type | Push-button |
| Colour | Pure white |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |



Complementary

| | |
|--------------------------------|--------------------------|
| Colour code | PW |
| Actuator | Push-button |
| Local signalling | Indicator light |
| Fixing mode | By screws |
| Material | PVC (polyvinyl chloride) |
| Surface finish | Glossy |
| [Ue] rated operational voltage | 250 V AC |
| Inrush current | 20 A |
| Height | 97.5 mm |
| Depth | 43.6 mm |
| Embedding depth | 31.6 mm |
| Width | 34 mm |
| Mounting position | Vertical |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.0 cm |
| Package 1 Width | 4.5 cm |
| Package 1 Length | 10.5 cm |
| Package 1 Weight | 80.0 g |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
