

Product data sheet

Characteristics

4064PB-PW

Push Button Switch, Saturn Series, 4 Gang, 250V, 16AX/20A

Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Colour	Pure white
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	PW
Actuator	Push-button
Local signalling	Without light indicator
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	116 mm
Depth	43.6 mm
Embedding depth	31.6 mm
Width	75 mm
Mounting position	Horizontal/vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	8 cm
Package 1 Length	11.5 cm
Package 1 Weight	191 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	128 cm
Package 2 Width	206 cm
Package 2 Length	260 cm
Package 2 Weight	2.116 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	No