

Product data sheet

Characteristics

4064PB-PW

Clipsal Saturn 4000, Push Button Switch, 4 Gang, 250V, 16AX/20A



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Colour	Pure white
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	PW
Actuator	Push-button
Local signalling	Without light indicator
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	116 mm
Depth	43.6 mm
Embedding depth	31.6 mm
Width	75 mm
Mounting position	Horizontal/vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	8 cm
Package 1 Length	11.5 cm
Package 1 Weight	191 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	128 cm
Package 2 Width	206 cm
Package 2 Length	260 cm
Package 2 Weight	2.116 kg
Package 3 Height	89.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile