

Product data sheet

Characteristics

4064PBL-PW

Switch Saturn - Assembled - LED indicator - 4-gang - 250 V - 20 A / 16 AX - Pure White



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Colour	Pure white
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	PW
Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	116 mm
Depth	43.6 mm
Embedding depth	31.6 mm
Width	75 mm
Mounting position	Horizontal/vertical

Packing Units

Package 1 Weight	0.201 kg
Package 1 Height	48.000 mm
Package 1 width	88.000 mm
Package 1 Length	120.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile