

## Product data sheet

### Characteristics

# 408/3A-WE

## SOCKET CLOCK 3PIN



### Main

Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
[In] rated current	5 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	30 mm
Length	106 mm
Width	59 mm
Fixing center	84 mm
Number of poles	1

### Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.04 kg
Package 1 Height	30 mm
Package 1 width	59 mm
Package 1 Length	106 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>