

Product data sheet

Characteristics

409/4-WE

Standard Series, Clock Point Plug, 4 PIN, 5A, 250V



Main

Product brand	Clipsal
---------------	---------

Complementary

[In] rated current	5 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Colour	Body: white electric
Plug, socket, control station shape	Angled
Duration	6 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	9.5 cm
Package 1 Length	11.4 cm
Package 1 Weight	36 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6.8 cm
Package 2 Width	8.4 cm
Package 2 Length	10.8 cm
Package 2 Weight	180 g
Unit Type of Package 3	CAR
Number of Units in Package 3	125
Package 3 Height	11.7 cm
Package 3 Width	25 cm
Package 3 Length	31 cm
Package 3 Weight	4.5 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile