

Product data sheet

Characteristics

40ADPSY-TN

adaptor RJ SystimaxaT&T, 10Pk



Main

Range	Clipsal Iconic
Product or component type	Adaptor
Product destination	Data socket



Complementary

Device mounting	Flush
Data socket type	RJ45 - 1 contacts
Number of gangs	1...6 gangs
Number of modules	1 module 23 x 23 x 12 mm
Fixing mode	Clip-in
Type of footprint	AT&T Systimax
Colour tint	Translucent (TN)
Surface finish	Glossy
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Material	ABS + PC: adaptor
Net weight	0.017 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.075 kg
Package 1 Height	3 cm
Package 1 width	12.5 cm
Package 1 Length	21 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
