

## Product data sheet

### Characteristics

# 40CSFM

Clipsal Iconic, selector switch, 4 positions, mechanism, Vivid White



#### Main

Range	Clipsal Iconic
Product or component type	Selector switch
Device application	Fan speed controller
Colour tint	Vivid white
Quantity per set	Set of 10

#### Complementary

Device presentation	Mechanism
Control type	Rotary knob
Switch function	4 positions
Marking	0 - 1 - 2 - 3
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	51 mm
Net weight	0.042 kg

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	50 g
Package 1 Height	31 mm
Package 1 width	73 mm
Package 1 Length	102 mm

#### Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.