

## Product data sheet

### Characteristics

# 40E2USBM-VW

Clipsal Iconic, 2 USB Charger, 40M, Type A, 2.1 A, 240 V, Vivid White



#### Main

Range	Clipsal Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	2 USB 2.0 type A 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	3.1 A




#### Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	Vivid white
Surface finish	Glossy
Fixing mode	Clipped
Type of packing	Box
Sale per indivisible quantity	1
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	5...90 %
Number of terminals	1 with cable end
Height	48 mm
Width	27 mm
Depth	59 mm
Embedding depth	55 mm

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	107.8 g
Package 1 Height	40 mm
Package 1 width	67 mm
Package 1 Length	85 mm

#### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

Environmental Disclosure

 [Product Environmental Profile](#)

---

Circularity Profile

 [End Of Life Information](#)

---