

## Product data sheet

### Characteristics

# 40M

## Clipsal Iconic, Switch Mechanism, 1-Way/2-Way 250V, 10AX



### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

### Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	1-pole 1/2-way
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	2.3 cm
Package 1 Length	3.2 cm
Package 1 Weight	16 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>