

## Product data sheet

### Characteristics

# 40M32COOK-VW

Switch Mechanism Cooker, Clipsal Iconic, 1-Way, 250V, 32A

### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Cooking appliances
Load type	Fluorescent 32 A LEDi lamp 277 W
Colour tint	Vivid white
Quantity per set	Set of 20


### Complementary

Device presentation	Mechanism
Control type	Rocker
Marking	Cooker
Rated current	32 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	5.1 cm
Package 1 Length	5.3 cm
Package 1 Weight	24 g
Unit Type of Package 2	CAR
Number of Units in Package 2	240
Package 2 Height	33.5 cm
Package 2 Width	26.1 cm
Package 2 Length	33.5 cm
Package 2 Weight	7440 g

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1