

Product data sheet

Characteristics

40MBPRL-VW

Clipsal Iconic, switch, mechanism, LED, 10 A, Vivid White



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Doorbell
Colour tint	Vivid white
Quantity per set	Set of 20



Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	1-pole 1/2-way
Marking	Press
Local signalling	LED indicator
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	22.0 g
Package 1 Height	4.5 cm
Package 1 width	6.8 cm
Package 1 Length	4.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
