

## Product data sheet

### Characteristics

# 40MD20

## Switch Mechanism, Clipsal Iconic, 1-Way, Double Pole, 20A, X



### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting Appliances Small motor loads
Load type	Fluorescent 20 A LEDi lamp 250 W
Colour tint	Vivid white
Quantity per set	Set of 20

### Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	2-pole 1-way
Rated current	20 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.306 cm
Package 1 Width	3.032 cm
Package 1 Length	3.29 cm
Package 1 Weight	26.08 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations