

## Product data sheet

### Characteristics

# 40MD20

Clipsal Iconic, switch, mechanism, 1 way, double pole, 20 A



### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting Appliances Small motor loads
Colour tint	Vivid white
Quantity per set	Set of 20

### Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	2-pole 1-way
Rated current	20 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	26.08 g
Package 1 Height	2.306 cm
Package 1 width	3.032 cm
Package 1 Length	3.29 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	0.522 kg
Package 2 Height	4 cm
Package 2 width	9 cm
Package 2 Length	15.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	300
Package 3 Weight	9032.2 g
Package 3 Height	33.5 cm
Package 3 width	26.1 cm
Package 3 Length	33.5 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>