

## Product data sheet

### Characteristics

# 40MD20COOK-VW

Clipsal Iconic, Switch Mechanism, COOKER,  
1-Way, Double Pole 250V, 20A, X



### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting Appliances Small motor loads
Load type	Fluorescent 20 A LEDi lamp 250 W
Colour tint	Vivid white
Quantity per set	Set of 20

### Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	2-pole 1-way
Marking	Cooker
Rated current	20 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	4.6 cm
Package 1 Length	10.1 cm
Package 1 Weight	30 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	32.8 cm
Package 2 Width	10.6 cm
Package 2 Length	14.6 cm
Package 2 Weight	715.6 g
Unit Type of Package 3	CAR
Number of Units in Package 3	240
Package 3 Height	33.5 cm
Package 3 Width	26.1 cm

Package 3 Length	33.5 cm
Package 3 Weight	7200 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>