

Product data sheet

Characteristics

40MI

Pro Series, switch, 40M, Intermediate, 250 V, 10 A

Main

Range	Pro Series
Product or component type	Switch
Device application	Lighting

Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	Intermediate
Rated current	10 A
[Ue] rated operational voltage	250 V
Fixing mode	By clips
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s)
Height	23 mm
Width	23 mm

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Package 1 Weight	15.98 g
------------------	---------

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile