

## Product data sheet

### Characteristics

# 40ML

## Clipsal Iconic, switch, mechanism, LED, 1 or 2-way, 10 A



### Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Colour tint	Vivid white
Quantity per set	Set of 20






### Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	1-pole 1/2-way
Local signalling	LED indicator
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	17.37 g
Package 1 Height	2.297 cm
Package 1 width	2.297 cm
Package 1 Length	16.654 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>