

## Product data sheet

### Characteristics

# 40RJ64SMT-TN

Clipsal Iconic, Data Socket, Category 3, 4  
Contact Telephone



### Main

Range	Actassi
Product or component type	Telephone socket
Device presentation	Insert

### Complementary

Device mounting	Flush
Provided equipment	Cable retention cap
Telephone socket type	RJ12 (4 contacts)
Cable stiffness	Solid
Colour tint	Translucent
Surface finish	Glossy
Type of packing	Polybag
Sale per indivisible quantity	1
Height	23 mm
Width	23 mm
Depth	28 mm
Net weight	0.006 kg
Standards	AS/NZS 3080 AS/CA S008






### Environment

Product certifications	RCM
------------------------	-----

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	3.7 cm
Package 1 Length	4.7 cm
Package 1 Weight	6.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations