

## Product data sheet

### Characteristics

# 40RJ64SMT-XW

Clipsal Actassi, Connector RJ12 4 Pin,  
Telephone Symbol



### Main

Range	Actassi
Product type	Modular jack
Device presentation	Two piece design
Colour tint	Connector housing: white (ABS + PC) Top cover: white (PC)
Wiring Colour configuration	RAL 9010
Type of packing	Individual bag
Quantity per set	Set of 1

### Complementary

Insulation resistance	Initial insulation resistance: > 500 MOhm at 100 V DC
Connector type	RJ12
AWG gauge	AWG 24...AWG 22
Durability	750 cycles
Contact pins	4 pins of copper alloy and gold plated conforming to IEC 60603-7
Tool type	Punch down tool
Cable outer diameter	0.8...1.4 mm
Compatible LAN cable types	UTP
Communication network category	3
Supported applications	10/100BASE-T
Connections - terminals	IDC
Product compatibility	RJ12 plug
Type of footprint	40 mech
Height	22 mm
Length	30 mm
Width	18 mm
Net weight	0.008 kg
Targeted region	Asia Pacific.

### Environment

Operational temperature range	-10...60 °C
Ambient air temperature for storage	-10...60 °C
Product certifications	RCM
Standards	ANSI/TIA-568-C.2 ISO/IEC 11801:2011 Ed.2.2 AS/NZS 3080:2003

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	3.7 cm
Package 1 Length	4.7 cm
Package 1 Weight	6.0 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------