

## Product data sheet

### Characteristics

# 40RSM3-VW

Selector switch, Clipsal Iconic, mechanism, 4 positions, Off 1 2 3, 10A 250V, Vivid White

#### Main

Range	Clipsal Iconic
Product or component type	Selector switch
Device application	Small appliances
Colour tint	Vivid white
Quantity per set	Set of 20

#### Complementary

Device presentation	Mechanism
Control type	Rotary knob
Switch function	4 positions
Marking	0 - 1 - 2 - 3
Rated current	10 A
[Ue] rated operational voltage	250 V
Connections - terminals	Screw terminal 1.5 Mm <sup>2</sup> screw terminal for 4 2.5 mm <sup>2</sup> screw terminal for 3
Height	23 mm
Width	23 mm
Depth	50 mm
Net weight	0.02 kg

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	24.0 g
Package 1 Height	3.3 cm
Package 1 width	3.1 cm
Package 1 Length	10 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	0.622 kg
Package 2 Height	13 cm
Package 2 width	10 cm
Package 2 Length	15.8 cm
Package 3 Height	33.5 cm