

Product data sheet

Characteristics

40USML

Clipsal Iconic, Switch Mechanism Universal Rocker , 250V, 20A, /16Ax1-Way/2-Way LED



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 20 A LEDi lamp 250 W
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	1-pole 1/2-way
Local signalling	LED indicator
Rated current	20 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.297 cm
Package 1 Width	2.297 cm
Package 1 Length	16.675 cm
Package 1 Weight	18 g
Unit Type of Package 2	PAL
Number of Units in Package 2	7200
Package 2 Height	950 cm
Package 2 Width	1140 cm
Package 2 Length	1140 cm
Package 2 Weight	129.6 kg
Package 3 Height	33.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations