

Product data sheet

Characteristics

412-WE

Single Socket Outlet, 250VAC, 10A, 3 PIN, Surface Mount



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
Surface finish	Glossy
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	28 mm
Diameter	47 mm
Fixing center	35...38 mm
Number of poles	1

Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	9 cm
Package 1 Length	12 cm
Package 1 Weight	40 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	10
Package 2 Height	6.8 cm
Package 2 Width	10 cm

Package 2 Length	13.4 cm
Package 2 Weight	0.444 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	21.4 cm
Package 3 Width	29.7 cm
Package 3 Length	42.9 cm
Package 3 Weight	12.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile