

## Product data sheet

### Characteristics

# 412L-WE

## SOCKET SURF 3PIN LIGHT 10A 250



### Main

Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	28 mm
Diameter	47 mm
Fixing center	35...38 mm
Number of poles	1

### Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>