

## Product data sheet

### Characteristics

# 413F-WE

## SOCKET SURFACE 3PIN 10A 250V



### Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	46 mm
Diameter	66 mm
Fixing center	50 mm
Number of poles	1

### Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	68.0 g
Package 1 Height	4.5 cm
Package 1 width	6.5 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	750.0 g
Package 2 Height	0.1 cm
Package 2 width	16.4 cm
Package 2 Length	16.5 cm

Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	7.8 kg
Package 3 Height	21 cm
Package 3 width	34.8 cm
Package 3 Length	44.5 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>