

## Product data sheet

### Characteristics

# 413QC-WE

## Single Socket Outlet, Standard Series, 250VAC, 10A, 3 PIN, Quick Connect, Surface Mount



### Main

|                           |                  |
|---------------------------|------------------|
| Product or component type | Socket-outlet    |
| Colour                    | White electric   |
| Product brand             | Clipsal          |
| Quantity per set          | Set of 1         |
| Cover type                | Complete housing |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Colour code                    | WE                      |
| Marking                        | Without marking         |
| Local signalling               | Without light indicator |
| Device mounting                | Surface                 |
| Fixing mode                    | By screws               |
| Material                       | Plastic                 |
| [In] rated current             | 10 A                    |
| [Ue] rated operational voltage | 250 V AC                |
| Network frequency              | 50 Hz                   |
| Depth                          | 46 mm                   |
| Length                         | 70 mm                   |
| Width                          | 47 mm                   |
| Fixing center                  | 50 mm                   |
| Number of poles                | 1                       |

### Environment

|           |                                   |
|-----------|-----------------------------------|
| Standards | AS 3109<br>AS 3100<br>AS/NZS 3112 |
|-----------|-----------------------------------|

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Height             | 4.8 cm |
| Package 1 Width              | 5 cm   |
| Package 1 Length             | 7 cm   |
| Package 1 Weight             | 54 g   |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant with Exemptions                     |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations      |